



*Trinocular phase contrast microscope,  
1000x, W-PLAN objectives*

<b>Observation Method - Transmitted Light</b>	Brightfield	Yes
	Phase contrast (Positive type)	Yes
	Darkfield	Yes
	Simple polarized light	As optional
<b>Main Body</b>	Type	Upright
	Construction material	Aluminum die-cast
	Trasportation handle	Yes
<b>Head</b>	Type	Trinocular (Siedentopf)
	Split ratio	50/50
	Inclination	30°
	360° rotating	Yes
	Interpupillary distance (mm)	48-75
	Dioptric adjustment	On left tube
	Fixing screw for eyepieces	Yes
	Tube inner diameter (mm)	23
<b>Eyepieces</b>	Field number (mm)	20
	Magnification	10x
	Pointer	As optional
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	21
	High eyepoint (for glass wearers)	Yes
	Rubber cup	Yes
<b>Nosepiece</b>	Positions	Quintuple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS
<b>Objectives</b>	Optical system	160
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	45
	Standard magnifications	40x-1000x
	Type	W-PLAN
		W-PLAN 4x/0.10, W.D. 15.8 mm
		W-PLAN PH 10x/0.25, W.D. 12.2 mm
		W-PLAN PH 40x/0.65, W.D. 0.37 mm
		W-PLAN PH 100x/1.25 (Oil), W.D. 0.13 mm
<b>Stage</b>	Type	Double layer
	Dimensions (mm)	150x139
	Moving mechanism	Rackless
	Moving range (mm)	75x33
	Material	Anti-scratch painting
	Specimen holder	Yes
	Slide number	1
	X-Y Vernier scale	Yes
	Vernier scale accuracy (mm)	0.1

<b>Condenser - Multiple Position</b>	Type	Abbe. Brightfield - Phase contrast - Darkfield (dry)
	Number of positions	5 (BF, 10x/20x, 40x, 100x, DF)
	Numerical aperture (N.A.)	1.25
	Removable	Yes
	Diaphragms	Iris
	Centrable	Yes
	Focusable	By rack and pinion

<b>Focusing System</b>	Type	Coaxial coarse & fine
	Coarse total travel (mm)	25
	Fine total travel (per single rotation) (mm)	0.2
	Fine graduations	100
	Fine resolution (µm)	2
	Upper stop to prevent contact	Yes
	Adjustable tension	Yes
	Flat knob for ergonomy	Yes

<b>Transmitted Illumination</b>	Kohler illumination	Fixed (full as optional)
	Type	X-LED
	X-LED type	X-LED3
	Light source power (W)	3.6
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	6

<b>Power Supply for Transmitted Illumination</b>	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	6 Vdc 2.5 A

<b>Accessories Included</b>	Dust cover	Yes
	Immersion oil (10ml)	Yes
	Tension adjustment tool	Yes
	Allen wrench	Yes
	Centering telescope	Yes
	Green filter	Yes
	User Manual	Digital version (downloadable)

<b>Additional Information</b>		External rechargeable battery pack (as optional).
-------------------------------	--	---

<b>Product Dimensions</b>	Height (mm)	405
	Width (mm)	235
	Depth (mm)	370

<b>Product Weight</b>	(kg)	7.8
-----------------------	------	-----